

# Demineraliser And Digital Water Condition Indicator



Using a readily available mixed bed ion exchange resin with our pressure vessel and meter is probably the simplest method of producing very pure water for your glass washing needs. Mains water is able to percolate through the resin before being monitored by an accurate conductivity meter before entering your machine.

## FEATURES

- ▶ Produces high quality water less than 5 Micro Seimens mS/cm.
- ▶ Water quality suitable for washing Low e glass, soft and hardcoat.
- ▶ No specialist knowledge or training required .
- ▶ No dangerous chemicals involved in the treatment process.
- ▶ Takes up minimal space:  
Vessel 200mm x 200mm x 1000mm
- ▶ Vessel suitable for low and high mains water pressure.

## OPTIONS

- ▶ Two sizes available : large 1000mm, small 650mm.
- ▶ Available prefilled with resin or empty

## CONTACT

### SALES

☎ 01455 251151  
✉ [sales@atlantic-machinery.co.uk](mailto:sales@atlantic-machinery.co.uk)

### STUART HEADINGTON

☎ 07803 758291  
✉ [s.headington@atlantic-machinery.co.uk](mailto:s.headington@atlantic-machinery.co.uk)